

GALLINACEOUS



TXE-124N

NECKLACE:

Used on at least 2,000 deployments without known event of transmitter coming out, this method is in use on Gallinaceous birds like Grouse, Chicken, Pheasant, Quail, etc.

Necklaces are to be used like collars, with the main difference that there is no belting, instead the head is passed through a hole made by the antenna, epoxy, a bib preferably made of vinyl-coated nylon, or a combination of these. The bib is made by the user and attached to the center hole, then the head of the bird is passed through. The transmitter is made so it lies flat over the chest, and whenever possible includes a "V" shape so it rests even better.

Other models than those listed available upon request.

If collars are preferred please download this file: <http://www.telenax.com/English/Products/Collar.pdf>

Model	Weight [gr]	Housing dimensions [mm] (dia=diameter)	RANGE vs LIFE			PRICE
			Range Without obstacles [km]	Lifetime (D-Days; M-Months; Y-Years)	Pulse width [ms] @ Pulses Per Minute	
TXB-009N	5.7	26x14x9	4	10 M & 25 D	25 @ 40	B
TXB-120N	6.5	21 dia x 9	20	7M & 10 D	25 @ 40	C
TXE-120N	7.2	21 dia x 10	30	50 D	30 @ 60	C
				73 D	30 @ 40	
			25	3 M & 15 D	20 @ 40	
				4 M & 15 D	20 @ 30	
TXE-203N	8.5	19 x 19 x 14	30	70 D	30 @ 60	D
				3 M & 10 D	30 @ 40	
			25	4 M & 25 D	20 @ 40	
				6 M & 5 D	20 @ 30	

Model	Weight [gr]	Housing dimensions [mm] (dia=diameter)	RANGE vs LIFE			PRICE
			Range Without obstacles [km]	Lifetime (D-Days; M-Months; Y-Years)	Pulse width [ms] @ Pulses Per Minute	
TXE-304N	9	12dia x 34	30	95 D	30 @ 60	D
				4 M & 15 D	30 @ 40	
			25	6 M & 15 D	20 @ 40	
				8 M & 10 D	20 @ 30	
TXE-207N	14	20 x 29 x 13	30	5 M	30 @ 60	D
				7 M & 7 D	30 @ 40	
			25	10 M & 10 D	20 @ 40	
				13 M & 10 D	20 @ 30	
TXE-124N	14	27dia x 11	30	3 M & 25 D	30 @ 60	D
				5 M & 15 D	30 @ 40	
			25	7 M & 25 D	20 @ 40	
				10 M	20 @ 30	
TXE-125N	18	27dia x 14	30	6 M & 20 D	30 @ 60	D
				9 M & 20 D	30 @ 40	
			25	13 M & 25 D	20 @ 40	
				17 M & 20 D	20 @ 30	

Sensors:

- TXB Models: No sensors available.
- TXE & TXF Models: Any of the following sensors available:
 - Activity / Inactivity
 - Mortality
 - Position

Activation:

- By removing a magnet.
- TXB-001 to TXB-004, TXB-110 & TXE-110: Activation is made by soldering two wires. Activation by magnet can be included but this will cause a small increase in weight and dimensions.

Weight and dimensions:

- Dimensions include electronics, battery and housing. Do not include bib or antenna.
- Weight includes all parts forming the system except for the bib.

Range:

- Without obstacles or LOS (Line of Sight). Detection range under ideal conditions including there are no obstacles between the transmitter and the receiving antenna.

Lifetime:

- Life is calculated over a mean temperature of 20° C (68° F).

Refurbishment:

- Once used, all our models are susceptible of refurbishment for a fraction of the cost of a new one.

Frequencies:

- Any frequency between 148 and 174 MHz. Frequencies between 216 to 222 MHz available except on models which start with TXB-0.

Warranty:

- Same time as estimated battery lifetime; minimum 2 months, maximum 18 months.

Price:

In order to get the price list please follow this link:

<http://www.telenax.com/English/Products/Prices.pdf>